

CommWatch II

Release Notes

8/31/2010

Rev. B2 firmware

This firmware update **requires** Version 2.3 or higher Software.

Changes have been made to improve performance after the following changes were made in Rev. B1/ Ver. 2.2: PRI D-channel storage to the USB Flash drive has been converted to "raw" data storage to increase speed and avoid lost buffers. As a result very busy D-channel operations (in excess of 4000 calls/hr) can be captured and stored. The files on the flash drive can no longer be interpreted using Notepad or similar text file display programs. The D-channel information displayed and captured internally by the CommWatch II retains the former functionality.

Version 2.3 Software

This software release is compatible with Rev B2 and all prior release versions of Firmware for the CommWatch II. Performance is improved after features were added in the last revision.

When D-channel data has been stored as "raw" data using the Rev. B2 firmware, this software will interpret the data and display decoded information.

Filter capability has been added to the software to allow Selection for CRV, Called Party Number, Calling Party Number, Cause Code and Call Duration.

Multiple files may be selected for decode using standard Windows techniques such as SHIFT + Click.

A Save to Text File function has been added to save the decoded (filtered) D-channel information in a report form.